

ENDURANCE SPORTS BRAII

Name ENDURANCE SPORTS BRA II

Style No. O17722C6

IRISH CREAM PEBBLE CAMO ALL OVER PRINT Description

Brand Division 10 TOPS Category Season Year 22

Size Scale -Sample size

XS S M L XL XXL

DEVELOPMENT STATUS

DELIVERY

1ST PTRN# Pattern Ref:O13722A3

1st Proto

CATEGORY **KNITS** SAMPLE SIZE S CUT QTY


DUE DATE 01-25-2022 COUNTRY OF ORIGIN CHINA Created by/Author 01-07-2022

undefined

emoore@johnnywas.com



Screen Shot 2022-01-07 at 2.25.06 PM




Strappy Bra-01

Interior Bra Construction

There are two layers to create the interior bra construction bra.

The layer closest to the self is approved power mesh.

The layer closest to the wearer's body is approved stretch lining.



interior bra construction-02


O, 10, TOPS, 3, 22



Calme_Final 2 ScreenPrint_made_in_CHINA

Logo Placement

Place logo centerd at back 3/4" down from back top edge



Not for color. Not to scale.

SCREEN PRINTING CALME ACTIVE-06

ENDURE SPORTS BRA Calme Hang Tag




Place on wearer's left side seam under the armhole, 1/2" down from Top Edge

Screen Shot 2021-12-31 at 2.13.17 PM

ENDURE SPORTS BRA Calme TPU Care Label

- DISCLAIMER
LABELING IS FOR
REFERENCE ONLY,
PLEASE PUT APPROPRAITE
COUNTRY OF ORIGIN
AND CARE & CONTENT
INFORMATION



Place on inside at wearer's left side seam, 2" from bottom

Screen Shot 2021-12-31 at 2.13.28 PM

Sample Size: S

| POINT OF MEASURE | CODE | HOW TO MEASURE | CRITICAL | TYPE | TOLERANCE | S |
|---|--------|--------------------------------|----------|------|-----------|-----------|
| FRONT BODY LENGTH | oouWkW | HIGH POINT BODICE TO HEM | true | Full | 1/4 in | 7 in |
| BACK BODY LENGTH | 389JOo | CB TOP EDGE TO HEM | true | Full | 1/4 in | 3 in |
| NECK WIDTH | EOcWpq | EDGE TO EDGE | true | Full | 1/8 in | 9 in |
| FRONT NECK DROP | e5zlql | HIGH POINT BODICE TO NECK EDGE | true | Full | 1/8 in | 1 1/2 in |
| CHEST WIDTH | Is5S13 | 1" BELOW AH | true | Full | 1/4 in | 13 3/4 in |
| BOTTOM OPENING WIDTH | jBglyR | ALONG BOTTOM EDGE | true | Half | 1/4 in | 13 5/8 in |
| BOTTOM BAND HEIGHT | EJ1fRN | SEAM TO EDGE | true | Full | 1/8 in | 3/4 in |
| STRAP WIDTH | BpLJCF | EDGE TO EDGE | true | Full | 1/8 in | 1/2 in |
| STRAP LENGTH | 36GF6I | FRONT HPB TO BOTTOM BARTACK | true | Full | 0 in | 13 1/4 in |
| FRONT ARMHOLE LENGTH | ByKyPE | SIDE SEAM TO FRONT HPB | true | Full | 1/4 in | 4 1/2 in |
| KEYHOLE WIDTH | 5BciPZ | AT WIDEST POINT | true | Full | 1/8 in | 3 3/4 in |
| KEYHOLE HEIGHT | 7SyRfK | STRAP BAR TACK TO CB TOP EDGE | true | Full | 1/8 in | 3 in |
| FRONT NECK LENGTH | GmqaiQ | INCLUDING BINDING | true | Full | 1/8 in | 10 3/4 in |
| PLACEMENT BETWEEN TOP BARTACK AND HIGH POINT BODICE | Bhqvea | | true | Full | 1/8 in | 9 in |
| PLACEMENT BETWEEN BARTACK | HuThug | | true | Full | 1/8 in | 2 in |
| PLACEMENT BETWEEN BOTTOM BARTACK AND HIGH POINT KEYHOLE | w8XpKf | | true | Full | 1/8 in | 3 in |

Sample Size: S

| POINT OF MEASURE | CODE | HOW TO MEASURE | CRITICAL | TYPE | TOLERANCE | S |
|---|--------|--------------------------------|----------|------|-----------|-----------|
| FRONT BODY LENGTH | oouWkW | HIGH POINT BODICE TO HEM | true | Full | 1/4 in | 7 in |
| BACK BODY LENGTH | 389JOo | CB TOP EDGE TO HEM | true | Full | 1/4 in | 3 in |
| NECK WIDTH | EOcWpq | EDGE TO EDGE | true | Full | 1/8 in | 9 in |
| FRONT NECK DROP | e5zlql | HIGH POINT BODICE TO NECK EDGE | true | Full | 1/8 in | 1 1/2 in |
| CHEST WIDTH | Is5S13 | 1" BELOW AH | true | Full | 1/4 in | 13 3/4 in |
| BOTTOM OPENING WIDTH | jBglyR | ALONG BOTTOM EDGE | true | Half | 1/4 in | 13 5/8 in |
| BOTTOM BAND HEIGHT | EJ1fRN | SEAM TO EDGE | true | Full | 1/8 in | 3/4 in |
| STRAP WIDTH | BpLJCF | EDGE TO EDGE | true | Full | 1/8 in | 1/2 in |
| STRAP LENGTH | 36GF6I | FRONT HPB TO BOTTOM BARTACK | true | Full | 0 in | 13 1/4 in |
| FRONT ARMHOLE LENGTH | ByKyPE | SIDE SEAM TO FRONT HPB | true | Full | 1/4 in | 4 1/2 in |
| KEYHOLE WIDTH | 5BciPZ | AT WIDEST POINT | true | Full | 1/8 in | 3 3/4 in |
| KEYHOLE HEIGHT | 7SyRfK | STRAP BAR TACK TO CB TOP EDGE | true | Full | 1/8 in | 3 in |
| FRONT NECK LENGTH | GmqaiQ | INCLUDING BINDING | true | Full | 1/8 in | 10 3/4 in |
| PLACEMENT BETWEEN TOP BARTACK AND HIGH POINT BODICE | Bhqvea | | true | Full | 1/8 in | 9 in |
| PLACEMENT BETWEEN BARTACK | HuThug | | true | Full | 1/8 in | 2 in |
| PLACEMENT BETWEEN BOTTOM BARTACK AND HIGH POINT KEYHOLE | w8XpKf | | true | Full | 1/8 in | 3 in |

Sample Size: S

| POINT OF MEASURE | CODE | HOW TO MEASURE | CRITICAL | TYPE | TOLERANCE |
|---|--------|--------------------------------|----------|------|-----------|
| FRONT BODY LENGTH | oouWkW | HIGH POINT BODICE TO HEM | true | Full | 1/4 in |
| BACK BODY LENGTH | 389JOo | CB TOP EDGE TO HEM | true | Full | 1/4 in |
| NECK WIDTH | EOcWpq | EDGE TO EDGE | true | Full | 1/8 in |
| FRONT NECK DROP | e5zlql | HIGH POINT BODICE TO NECK EDGE | true | Full | 1/8 in |
| CHEST WIDTH | ls5S13 | 1" BELOW AH | true | Full | 1/4 in |
| BOTTOM OPENING WIDTH | jBglyR | ALONG BOTTOM EDGE | true | Half | 1/4 in |
| BOTTOM BAND HEIGHT | EJ1fRN | SEAM TO EDGE | true | Full | 1/8 in |
| STRAP WIDTH | BpLJCF | EDGE TO EDGE | true | Full | 1/8 in |
| STRAP LENGTH | 36GF6I | FRONT HPB TO BOTTOM BARTACK | true | Full | 0 in |
| FRONT ARMHOLE LENGTH | ByKyPE | SIDE SEAM TO FRONT HPB | true | Full | 1/4 in |
| KEYHOLE WIDTH | 5BciPZ | AT WIDEST POINT | true | Full | 1/8 in |
| KEYHOLE HEIGHT | 7SyRfK | STRAP BAR TACK TO CB TOP EDGE | true | Full | 1/8 in |
| FRONT NECK LENGTH | GmqaiQ | INCLUDING BINDING | true | Full | 1/8 in |
| PLACEMENT BETWEEN TOP BARTACK AND HIGH POINT BODICE | Bhqvea | | true | Full | 1/8 in |
| PLACEMENT BETWEEN BARTACK | HuThug | | true | Full | 1/8 in |
| PLACEMENT BETWEEN BOTTOM BARTACK AND HIGH POINT KEYHOLE | w8XpKf | | true | Full | 1/8 in |

| | THUMBNAIL | COMPONENT | QTY | PLACEMENT | NOTES | MULTI CODE: MTI | | | |
|---|-------------|--|-----|--|---|--|--|--|--|
| | FABRICATION | | | | | | | | |
| 1 | | IRISH CREAM PEBBLE CAMO ON COMPRESSION ACTIVE FABRIC (AAG) CODE: DPS022J Content: 71% Polyester 29% Spandex Supplier: ACTIVE APPAREL GROUP Construction: INTERLOCK | | SELF | CUT AND PRINT ON CROSS GRAIN, RANDOM PRINT | MULTI Custom Code: MTI | | | |
| 2 | | SOLID ACTIVE COMPRESSION FABRIC (AAG) CODE: DPS022J Content: 71% Polyester 29% Spandex Supplier: ACTIVE APPAREL GROUP Construction: INTERLOCK | | CONTRAST 1: BOTTOM BAND | | Bordeaux Custom Code: 17-1710 TCX | | | |
| 3 | * | KNIT SPORTS BRA LINER (AAG) CODE: JNS079 Supplier: ACTIVE APPAREL GROUP Content: 91% NYLON 9% ELASTANE | | LINING, WILL BE USED ON FRONT AND BACK OF | DTM GROUND | IRISH CREAM Custom Code: 14-1208 TCX | | | |
| 4 | | 4-WAY POWER MESH (AAG) CODE: MNS063 Content: 85 % NYLON 15% SPANDEX Supplier: ACTIVE APPAREL GROUP Construction: WARP MESH | | PLACE IN SHELF BRA | DTM GROUND | IRISH CREAM Custom Code: 14-1208 TCX | | | |
| | TRIM | | | | | | | | |
| 5 | ©. | CALME SCREEN PRINT LOGO REFLECTIVE CODE: MO2W5 | 1 | PLACE ON CB | FOLLOW LABEL GUIDE FOR EXACT PLACEMENT, LOGO SIZE: 3/4" | Pewter Custom Code: 18-5203 TCX SIZE: 3/4" | | | |
| 6 | | SPORTS BRA CUPS (AAG) CODE: TD1530 | 2 | REMOVABLE CUPS, FOLLOW CALL OUT GUIDE FOR PLACEMENT | | BLACK Custom Code: BLK | | | |

| | THUMBNAIL | COMPONENT | QTY | PLACEMENT | NOTES | CODE: MTI | | | |
|----|--|--|-----|---|---|---|--|--|--|
| 7 | * | STRETCH ELASTIC FOR SPORTS BRA (AAG) CODE: EPR238 Supplier: ACTIVE APPAREL GROUP | | INSIDE BOTTOM EDGE | 3/4" width / FOLLOW TECH SHEET FOR PLACEMENT | 3/4" BLACK ELASTIC | | | |
| 8 | | 3/8" SOFT ELASTIC CODE: 3UxyY | 2 | INSIDE EACH SHOULDER STRAP | | BLACK Custom Code: BLK | | | |
| | | | | THREAD | | | | | |
| 9 | | Sewing Threads (DTM POLY THREAD) CODE: C00049 | | DTM SELF | | - | | | |
| | | | · | LABELS AND HANGTAGS | | | | | |
| 10 | Caline Working the HOUSE We After 1990 When 1990 Washington to the State of the | CALME SCREEN PRINT LABEL- LOGO /SIZE /COUNTRY OF ORIGIN CODE: nMdei | 1 | ON INSIDE OF CB, CENTERED, 1" FROM TOP EDGE/NECK | Please follow the image attached. artwork ai file sent via email | - | | | |
| 11 | Calme I see the second | TPU CARE LABEL FOR CALME (AAG) CODE: TD1704 Supplier: ACTIVE APPAREL GROUP | 1 | WEARER'S LEFT- 2" above the hem | FOLLOW ATTACHED LABEL PLACEMENT | - | | | |
| 12 | | NEW CALME HANGTAG CODE: TOP CARD- CALME-T01P, BOTTOM CARD- CALME-T02 | 1 | left SS UNDER THE ARMHOLE | ATTACHED LABEL PLACEMENT | - NEW CALME HANGTAG- TOP CARD- CALME-T01P, BOTTOM CARD- CALME-T02 n/a | | | |
| | Components 12 | | | | | | | | |
| | | | | | | | | | |